



TXA224

## Output device for 4 shutters or blinds 230V~

### Technical properties

#### Architecture

|                                   |     |
|-----------------------------------|-----|
| Bus system                        | KNX |
| Number of blinds/shutters outputs | 4   |

#### Functions

|                       |    |
|-----------------------|----|
| Bus module detachable | No |
|-----------------------|----|

#### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

#### Controls and indicators

|                |     |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

#### Main electrical features

|                        |    |
|------------------------|----|
| Type of supply voltage | DC |
|------------------------|----|

#### Voltage

|                       |                |
|-----------------------|----------------|
| System supply voltage | 30V DC via bus |
|-----------------------|----------------|

#### Electric current

|                           |     |
|---------------------------|-----|
| Number of entry circuits  | 0   |
| Maximum switching current | 6 A |

#### Power

|                                  |        |
|----------------------------------|--------|
| Contact rating with 230 V in AC1 | 1380 W |
| Total power loss under IN        | 2 W    |

#### Connection

|   |                           |
|---|---------------------------|
| Connection cross-sect. flexible conductor | 0,75 / 2,5mm <sup>2</sup> |
| Connection cross-sect. rigid cable        | 0,75 / 2,5mm <sup>2</sup> |
| Number of contacts                        | 4                         |
| Type of connection                        | quick connect             |

#### Scope of delivery

|                         |     |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

#### Equipment

|                               |    |
|-------------------------------|----|
| Bidirectional radio frequency | No |
|-------------------------------|----|

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | 0...45 °C   |
| Storage/transport temperature | -20...70 °C |

