

# ECR300C

3 Phase kWhmeter via CT 1A or 5A 4M MODBUS MID

## Architecture

Bus system	MODBUS
Number of poles	4 P
Type of pole	3P+N
Fixing mode	DIN rail type O (symmetrical)

## Main electrical features

Rated operational voltage Ue	92 / 480 V
Frequency	50 Hz
Rated current	5 A
Type of supply voltage	AC

## Voltage

Max operating voltage	300 V
Rated impulse withstand voltage 6 kV	

## Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	90 mm
Width of installed product	72 mm
Power	
Power consumed	2 VA
Total power loss under IN	0.6 W
Measurement	
Type of measuring instrument	electronical
Capacity	
Number of modules	4
Power supply	
Supply voltage	400 V $\pm$ 20%
Installation, mounting	
Tightening torque	0.5Nm
Mounting type	din-Rail
Equipment	
Type of display	retro illuminated display
Type of counter	4 wires counter
Standards	
Standard text	EN 50470-1 ; 3 ; IEC 62053-21 ; 23 ; IEC 61557-12
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Protection class	isol.class II
Use conditions	
Operating temperature	-25/55 °C
Storage temperature	-25/70 °C
Temperature	
Operating temperature	-25/55 °C