



Relay 16A, 1NO+1NC, 24V~50Hz

Technical Characteristics

Rated operational voltage Ue	230 V
Frequency	50 Hz
Rated current	16 A
Rated insulation voltage	250 V
Rated impulse withstand voltage	4 kV
Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm
Total power loss under IN	3.9 W
Power dissipation per coil	2.9 W
Electric endurance in number of cycles	30000
Number of mechanical operations	100000
Number of modules	1
Max. power with fluorescent parallel lamps	490 VA
Max. power with incandescent lamps	1100 W
Tightening torque	1,2Nm
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 10mm ²
Type of contacts	1NC+1NO
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2X
Operating temperature	-10 °C 50 °C