


TYA608B



**Output module 8x 10A /230V~, KNX**

**Technical properties**

**Architecture**

Bus system	yes
Fixing mode	REG

**Functions**

Multi-phase mode	suitable to switch different external conductors
Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function
Switching	for switching, e.g. of 8 independent loads or activation of 4 drives
Operating mode	any combined operation from drive and switching functions possible

**Configuration**

Number of modules	6
-------------------	---

**Controls and indicators**

Indicator lamp	yes
Operation	Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; manual operation per channel using button (single-area operation)
Indication / display	status LED integrated in the manual operation button
Manual selection switches / push-buttons	manual operation buttons for on/off (up/down) and bus function on/off per channel/device
Button / push-button	with illuminated programming button

**Main electrical features**

Rated current	10 A
---------------	------

**Voltage**

Operating voltage over bus	21...32 V DC
Output voltage	230 V~
System supply voltage	30V DC via bus

**Electric current**

Bus current consumption (data transfer)	15 mA
Bus current consumption (idle)	9 mA
Number of entry circuits	0
Maximum through current	10 A
Switching current at $\cos \varphi = 0.8$	max. 10 A

**Dimensions**

Width of rail mounted device (RMD)	6 modules
Height	90 mm
Width	105 mm

**Power**

Max. power with electronic transfo.	1000 W
Total power loss under IN	6 W
Output power	1200 W
Conventional transformers	1200 VA
Electronic transformers	1000 W

**Lighting control**

Fluorescent lamps with electronical ballast (EB)	15 x 36 W
- uncompensated	1000 VA

**Fluorescent bulbs control**

Energy-saving lamps	12 x 23 W
Power lighting fluo lamps	12x23W
Max. power fluo. duo lamp comp. series	15 x 36 W

**LED control**

Max number of LED/CFL lamps	12
230V LED lamps	12 x 23 W
Power LED	144 W
LED	Status LED integrated in manual operation button

**Incandescent bulbs control**

Max. power with incandescent lamps	1200 W
230 V incandescent lamps	1200 W
230 V halogen lamps	1200 W
230 V incandescent lamps and halogen lamps	1200 W

**Connection**

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of contacts	8NO
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

**Settings**

Supported configuration modes	system
Setting	switching time on change of direction adjustable

---

**Scope of delivery**

Bus connection included Yes

---

**Equipment**

Modular expandability No

---

**Use**

Differentiation characteristic 3 - Sales with plug-in terminals

---

**Safety**

Protection index IP IP20

---

**Use conditions**

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C

---

**Identification**

Main design line KNX