

CEA225U

RCCB 2P 25A 100mA A Class



- Architecture
 - Neutral position right
 - Number of poles 2 P
 - Fixing mode DIN rail type O (symmetrical)
- Main electrical features
 - Rated operational voltage U_e 230 V
 - Frequency 50 Hz
 - Rated current 25 A
- Voltage
 - Rated insulation voltage 500 V
 - Rated impulse withstand voltage 4000 V
- Electric current
 - Rated residual operating current 100 mA
 - Breaking and opening capacity 1500 A
 - Rated conditional short-circuit current I_{nc} according to EN 61008-1 6 kA
- Electric current / temperature

- Rating current 30°C
25 A
- Dimensions
 - Depth of installed product
70 mm
 - Height of installed product
83 mm
 - Width of installed product
35 mm
- Power
 - Total power loss under IN
1.3 W
- Tripping
 - Short-time delayed tripping
No
 - Residual current trip mode
Undelayed
- Endurance
 - Electric endurance in number of cycles
2000
 - Number of mechanical operations
4000
- Capacity
 - Number of modules
2
- Installation, mounting
 - Tightening torque
2,8Nm
- Connection
 - Connection cross-sect. flexible conductor
1 ; 16mm²
 - Connection cross-sect. rigid cable
1 ; 25mm²
 - Type of connection
with screw
- Standards
 - Standard text
BS 61008-1 ; EN 61008-1
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
 - Residual current type
A
- Use conditions
 - Operating temperature
-25/40 °C
 - Storage temperature
-55/70 °C
- Temperature
 - Operating temperature
-25/40 °C