



Weekly time switch 1 channel, 12/24V, digital, 2 modules

Technical Characteristics

Fixing mode	Din-Rail
Function	Presence simulation Keylock by means of blocking key with pulse function
Switch mode	change-over contact
Rated operational voltage Ue	12 V 24 V
Frequency	50 Hz
Supply voltage	12/24V AC/DC
Depth of installed product	64 mm
Height of installed product	85 mm
Length	85 mm
Width of installed product	35 mm
Dimensions (W x H x D)	64 mm 35 mm 85 mm
Power consumed	0.8 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W
Breaking capacity	16A 250V AC1
Number of modules	2
Power reserve [years]	≈ 5 a
Max. power with incandescent lamps	2300 W
Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	1X7D.
Number of channels	1
Supply failure reserve	5 years
With holidays program	Yes
DCF	No

Cycle	weekly
Protection index IP	IP20
Operating temperature	45 °C -5 °C
Working accuracy	1,5