

ST313

Safety transformer 16VA 230V12-24V

Architecture

Fixing mode	DIN rail type O (symmetrical)
-------------	-------------------------------

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Frequency	50 Hz
-----------	-------

Voltage

Rated insulation voltage	4000 V
--------------------------	--------

Dimensions

Depth of installed product	58 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

Power

Power consumed	16 VA
----------------	-------

Total power loss under IN	1.5 W
---------------------------	-------

Capacity

Number of modules	4
-------------------	---

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	4mm ²
---	------------------

Connection cross-sect. rigid cable	6mm ²
------------------------------------	------------------

Standards

Standard text	EN 61558-2-6
---------------	--------------

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Temperature

Operating temperature	-20/35 °C
-----------------------	-----------
