



VD101NT

Sm.distr.,VD/IC<sup>2</sup>,surface,1row,1M,IP30,no terminals,AUS,without door

#### Technical properties

#### Functions

With a pipe-in lead	Yes
---------------------	-----

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	400 V
-----------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Depth of installed product	71 mm
----------------------------	-------

Internal depth	72 mm
----------------	-------

Height of installed product	163.5 mm
-----------------------------	----------

Width of installed product	27.5 mm
----------------------------	---------

Width in division units	1
-------------------------	---

#### Cover, door

Type of door closing	non keylock
----------------------	-------------

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Transparent cover or door	No
---------------------------	----

#### Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	plastic
----------	---------

Type of surface treatment	untreated
---------------------------	-----------

#### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

#### Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

#### Equipment

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

#### **Standards**

European directive WEEE	not concerned
-------------------------	---------------

#### **Safety**

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	Yes

#### **Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------