



Moulded Case Circuit Breaker h630 4P 70kA 400A LSI

Technical Characteristics

Number of poles	4 P
Type of pole	4P4D N:0;50;100%
Rated operational voltage Ue	220 V 690 V
Frequency	50/60 Hz
Rated current	400 A
Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V
Total power loss under I _N	62.4 W
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Number of modules	10.5
Interlockable	No
Tightening torque	22Nm
Connection cross-sect. flexible conductor	35 / 240mm ²
Connection cross-sect. rigid cable	35 / 240mm ²
Type of connection	Terminal
Can be accessorized	No
Standard text	IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP4X
Operating temperature	-25 °C 70 °C