



VE106H

vector,IP65,6-8M,UV-stabil,DC/AC,with knockouts

### Technical properties

#### Functions

With a pipe-in lead	Yes
---------------------	-----

#### Configuration

Number of modules	6
-------------------	---

#### Main electrical features

Nominal voltage	400 V
-----------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Depth of installed product	113 mm
Internal depth	113 mm
Height of installed product	190 mm
Width of installed product	165 mm
Width in division units	6
Thickness of sidewall material	2.5 mm

#### Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

#### Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	plastic
Type of surface treatment	untreated

#### Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

#### Connection

Number of conduit inlets	3
--------------------------	---

Subject to technical modifications

**Settings**

---

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

---

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	16
Extension possible	No
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

**Safety**

---

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C
REACH conform	No
RoHS conform	Yes

**Use conditions**

---

Operating temperature	-25...40 °C
-----------------------	-------------