

TRM691E

Module 1 flush mounted dimmer 200W, 2 wires + 2 inputs, KNX radio



- Architecture
 - Bus system
yes
- Functions
 - Function
reset function (to factory setting)
- Controls and indicators
 - Indicator lamp
yes
- Connectivity
 - Bus system radio frequent
Yes
- Voltage
 - Supply voltage
230V AC
 - Operating voltage
230 V AC
- Fuse
 - Fuse
short-circuit and overload proof (electronic fuse)
- Dimensions
 - Height
38 mm
- Incandescent bulbs control
 - Max. power with incandescent lamps
200 W
- Connection

- Connection cross-sect. flexible conductor
0,5 / 1,5mm²
- Connection cross-sect. rigid cable
0,5 / 2,5mm²
- Type of load
universal
- Type of connection
with screw
- Number of contacts
1
- Type of connection
with screw-in lift terminals
- Equipment
 - Dimming principle
phase cut-on or cut-off according to load type, self-learning
- Use conditions
 - Storage temperature
-25/70 °C
- Temperature
 - Operating temperature
-15/45 °C
- Identification
 - Designation syntax: Core designation/function
Dim actuator
 - Application, usage
KNX radio - actuators