



VE110H

vector,IP65,8-10M,UV-stabil,DC/AC,with knockouts

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	10
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	114 mm
----------------------------	--------

Internal depth	114 mm
----------------	--------

Height of installed product	210 mm
-----------------------------	--------

Width of installed product	237 mm
----------------------------	--------

Width in division units	10
-------------------------	----

Thickness of sidewall material	2.5 mm
--------------------------------	--------

Cover, door

Identification of protection index	65
------------------------------------	----

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	Yes
---------------------------	-----

Materials

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Material	plastic
----------	---------

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Subject to technical modifications

Connection

Number of conduit inlets	6
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	20
--------------------------------------	----

Extension possible	No
--------------------	----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	Yes
---------------------	-----

Safety

IK protection code against mechanical impacts	IK07
---	------

Protection class	isol.class II
------------------	---------------

Glow wire test	according EN 60695-2-11: 850°C
----------------	--------------------------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------