



VE212H

vector,IP65,24M,UV-stabil,DC/AC,with knockouts

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	24
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	151 mm
Internal depth	151 mm
Height of installed product	427 mm
Width of installed product	310 mm
Width in division units	24
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Subject to technical modifications

Connection

Number of conduit inlets	12
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	2
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	2
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	46
--------------------------------------	----

Extension possible	No
--------------------	----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	Yes
---------------------	-----

Safety

IK protection code against mechanical impacts	IK08
---	------

Protection class	isol.class II
------------------	---------------

Glow wire test	according EN 60695-2-11: 850°C
----------------	--------------------------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------