



VF118PT



**Small distributor,golf,flush,1row,18M,IP40,MS-terminal,Australia,N+PE,white door**

### Technical properties

#### Architecture

Fixing mode flush-mounting

#### Functions

With a pipe-in lead Yes

#### Configuration

Number of modules 18

#### Main electrical features

Nominal voltage 400 V

#### Electric current

Rated current 80 A

#### Dimensions

Insertion depth 72 mm

Depth of wall niche 72 mm

Depth of installed product 97.5 mm

Internal depth 97.5 mm

Height of installed product 293 mm

Installation height 257 mm

Width of installed product 460 mm

Width in division units 18

Built-in height 257 mm

Built-in width 426 mm

#### Cover, door

Type of door closing Latch

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

#### Materials

Colour pure white

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated
<b>Installation, mounting</b>	
Suitable for outdoor use	No
<b>Settings</b>	
Enclosure type	Distributor empty cabinet
<b>Equipment</b>	
Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes
<b>Standards</b>	
GWT Glow wire test	850 °C
European directive WEEE	concerned
<b>Safety</b>	
IK protection code against mechanical impacts	07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-25...40 °C