

# SBN263

## 2-pole, 63A Modular Switch

### Architecture

Neutral position	without neutral
Number of poles	2 P
Type of pole	2 P

### Main electrical features

Rated operational voltage Ue	400 V
Frequency	50;60 Hz
Rated current	63 A

### Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	6000 V

### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power	
Total power loss under IN	4.6 W
Endurance	
Electrical durability at nominal load in AC22 in operating cycles 5000	
Number of mechanical operations	60000
Capacity	
Number of modules	2
Installation, mounting	
Tightening torque	2,8Nm
Connection	
Connection cross-sect. flexible conductor	2,5 ; 16mm <sup>2</sup>
Connection cross-sect. rigid cable	2,5 ; 25mm <sup>2</sup>
Type of connection	with screw
Equipment	
Can be accessorized	No
Standards	
Standard text	IEC 60947-3 ; IEC ; EN 60669-2 ; IEC ; EN 60669-4
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Use conditions	
Storage temperature	-40/80 °C
Temperature	
Operating temperature	-20/50 °C