



WBMDUPB

**Mechanism push dimmer trailing-edge**

**Technical properties**

**Architecture**

Type of control unit Push button

**Main electrical features**

Nominal voltage 230 V

Frequency 50 Hz

**Voltage**

Operating voltage 230 V~ +10%/-15%

**Fuse**

Fuse short-circuit and overload proof (electronic fuse)

**Dimensions**

Depth 51 mm

Height 24 mm

Width 24 mm

**Power**

Power consumption (standby) max. 0.1 W

Electronic transformers 20...350 W

**Measurement**

Extension unit input with extension unit input for slave push-button  
WBMSLL

**Materials**

Colour white

**LED control**

Dimmable 230 V LED lamps 2.5...250 W

LED with blue status LED

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps 7...300 W

**Installation, mounting**

Installation mode RotoLoc ®

**Connection**

Conductor cross-section 1.5 mm<sup>2</sup>

---

**Cable**

Cable length, extensions	max. 20 m
--------------------------	-----------

---

**Equipment**

On/Off switch	Yes
---------------	-----

Dimming principle	phase cut-off
-------------------	---------------

Brightness	with brightness memory
------------	------------------------

---

**Safety**

Halogen free	Yes
--------------	-----

---

**Use conditions**

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Temperature	with overheating protection
-------------	-----------------------------

---

**Identification**

Main design line	Mechanisms
------------------	------------