

:hager

## Contactor 25A 1NC+1NO 24V

### Technical Characteristics

|  |                         |
|--|-------------------------|
| Rated operational voltage Ue               | 250 V                   |
| Frequency                                  | 50/60 Hz                |
| Rated insulation voltage                   | 250 V                   |
| Rated impulse withstand voltage            | 4 kV                    |
| Acceptable current rating with AC1         | 20 A                    |
| Depth of installed product                 | 58 mm                   |
| Height of installed product                | 85 mm                   |
| Width of installed product                 | 17.5 mm                 |
| Contact rating with 230 V in AC1           | 4000 W                  |
| Total power loss under IN                  | 1.95 W                  |
| Power dissipation per coil                 | 0.76 W                  |
| Electric endurance in number of cycles     | 30000                   |
| Number of mechanical operations            | 1000000                 |
| Number of modules                          | 1                       |
| Max. power with fluorescent parallel lamps | 1000 VA                 |
| Max. power fluo. duo lamp comp. series     | 1000VA                  |
| Max. power with incandescent lamps         | 2500 W                  |
| Connection cross-sect. flexible conductor  | 1 / 6mm <sup>2</sup>    |
| Connection cross-sect. rigid cable         | 1,5 / 10mm <sup>2</sup> |
| Type of connection                         | with screw              |
| Number of contacts                         | 2                       |
| Type of contacts                           | 1NC+1NO                 |
| Can be accessorized                        | No                      |
| European directive WEEE                    | not concerned           |
| Protection index IP                        | IP20                    |