

# VM12020K

Consumer unit, Design 30, dual row, 20+20way, 100A, switch disconnector income, KO

## Architecture

|             |                  |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

## Main electrical features

|               |       |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

## Dimensions

|                            |        |
|----------------------------|--------|
| Depth of installed product | 105 mm |
|----------------------------|--------|

|                             |        |
|-----------------------------|--------|
| Height of installed product | 480 mm |
|-----------------------------|--------|

|                            |        |
|----------------------------|--------|
| Width of installed product | 471 mm |
|----------------------------|--------|

## Capacity

|                   |    |
|-------------------|----|
| Number of modules | 40 |
|-------------------|----|

## Cover, door

|                      |             |
|----------------------|-------------|
| Type of door closing | non keylock |
|----------------------|-------------|

|               |    |
|---------------|----|
| Interlockable | No |
|---------------|----|

## Materials

|                   |      |
|-------------------|------|
| RAL colour number | 9010 |
|-------------------|------|

|          |       |
|----------|-------|
| Material | Steel |
|----------|-------|

Equipment

|                |   |
|----------------|---|
| Number of rows | 2 |
|----------------|---|

|                     |    |
|---------------------|----|
| Can be accessorized | No |
|---------------------|----|

Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

|                     |       |
|---------------------|-------|
| Protection index IP | IP2XC |
|---------------------|-------|