




WBME5A



## Mechanism, 5A electronic push button

### Technical properties

#### Main electrical features

Frequency 50 Hz

#### Power

Dimmable conventional transformers max. 500 VA

Power consumption (standby) ≤ 0.35 W

Electronic transformers max. 500 W

#### Measurement

Extension unit input with extension unit input for slave push-button WBMESL

#### Fluorescent bulbs control

Compact fluorescent lamps max. 500 VA

#### LED control

LED with configurable status LED (orange/blue)

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps max. 1200 W

#### Installation, mounting

Installation mode RotoLoc ®

#### Connection

Screw terminals (max.) 2 x 1,5/1 x 2,5 mm<sup>2</sup>

Type of connection with screw terminals

#### Cable

Cable length, extensions max. 40 m

#### Safety

REACH conform Yes

RoHS conform Yes

#### Use conditions

Operating temperature 5...40 °C

Storage/transport temperature -20...60 °C

#### Identification

Main design line silhouette