

# NRN406

MCB 4P 25kA C-6A 4M

:hager

- Architecture
  - Neutral position without neutral
  - Number of poles 4 P
  - Type of pole 4 P
  - Fixing mode Din-Rail
  - Curve C
- Main electrical features
  - Rated current 6 A
  - Type of supply voltage AC
- Voltage
  - Rated insulation voltage 500 V
  - Max operating voltage 415 V
  - Rated impulse withstand voltage 6000 V
- Electric current
  - Rated service breaking capacity Ics AC according IEC 60898-1 7.5 kA
  - Rated service breaking capacity Ics under 400V AC according IEC 60947-2

7.5 kA

- Dimensions
  - Depth of installed product  
70 mm
  - Height of installed product  
83 mm
  - Width of installed product  
70 mm
- Power
  - Total power loss under IN  
5.44 W
- Endurance
  - Electric endurance in number of cycles  
4000
  - Number of mechanical operations  
20000
- Capacity
  - Number of modules  
4
- Installation, mounting
  - Tightening torque  
2,8Nm
- Equipment
  - Can be accessorized  
Yes
- Standards
  - Standard text  
IEC 60947-2
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-25/80 °C
- Temperature
  - Operating temperature  
-25/70 °C