

NQN406

MCB 4P 25kA B-6A 4M

:hager

- Architecture
 - Neutral position without neutral
 - Number of poles 4 P
 - Type of pole 4 P
 - Fixing mode Din-Rail
 - Curve B
- Main electrical features
 - Rated current 6 A
 - Type of supply voltage AC
- Voltage
 - Rated insulation voltage 500 V
 - Max operating voltage 415 V
 - Rated impulse withstand voltage 6000 V
- Electric current
 - Rated service breaking capacity I_{cs} AC according IEC 60898-1 7.5 kA
 - Rated service breaking capacity I_{cs} under 400V AC according IEC 60947-2

7.5 kA

- Dimensions
 - Depth of installed product
70 mm
 - Height of installed product
83 mm
 - Width of installed product
70 mm
- Power
 - Total power loss under IN
5.44 W
- Endurance
 - Electric endurance in number of cycles
4000
 - Number of mechanical operations
20000
- Capacity
 - Number of modules
4
- Installation, mounting
 - Tightening torque
2,8Nm
- Equipment
 - Can be accessorized
Yes
- Standards
 - Standard text
IEC 60947-2
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-25/80 °C
- Temperature
 - Operating temperature
-25/70 °C