



WBME5A



Mechanism, 5A electronic push button

Technical properties

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
--------	-------

Power

Power consumption standby	0,35 W
230 V incandescent and halogen lamp	1200 W

Use conditions

Operating temperature	5 - 40 °C
-----------------------	-----------

Texts

Extension unit input	With extension unit input for slave push-button WBMESL
Installation mode	RotoLoc®
Type of connection	With screw terminals