

# NGT703

MCB 1P+N 6/10kA D-3A 1M

:hager

- Architecture
  - Neutral position  
left
  - Number of poles  
2 P
  - Type of pole  
1P+N
  - Curve  
D
- Main electrical features
  - Frequency  
50/60 Hz
  - Rated current  
3 A
  - Type of supply voltage  
AC
- Voltage
  - Rated insulation voltage  
500 V
  - Max operating voltage  
253 V
  - Rated impulse withstand voltage  
4000 V
- Electric current
  - Rated service breaking capacity Ics AC according IEC 60898-1  
6 kA
- Electric current / temperature

- Rating current 30°C  
3 A
- Dimensions
  - Depth of installed product  
70 mm
  - Height of installed product  
84.7 mm
  - Width of installed product  
17.7 mm
- Power
  - Total power loss under IN  
2.3 W
- Endurance
  - Electric endurance in number of cycles  
4000
  - Number of mechanical operations  
20000
- Capacity
  - Number of modules  
1
- Installation, mounting
  - Tightening torque  
1,9Nm
- Connection
  - Type of connection  
with screw
- Standards
  - Standard text  
EN 60898-1
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-25/80 °C
- Temperature
  - Operating temperature  
-25/60 °C