

MFN725

MCB 1P+N 3kA C-25A 1M

:hager

- Architecture
 - Neutral position
left
 - Number of poles
2 P
 - Type of pole
1P+N
 - Curve
C
- Main electrical features
 - Frequency
50/60 Hz
 - Rated current
25 A
 - Type of supply voltage
AC
- Voltage
 - Rated insulation voltage
500 V
 - Max operating voltage
253 V
 - Rated impulse withstand voltage
4000 V
- Electric current
 - Rated service breaking capacity Ics AC according IEC 60898-1
3 kA
- Electric current / temperature

- Rating current 30°C
25 A
- Dimensions
 - Depth of installed product
70 mm
 - Height of installed product
84.7 mm
 - Width of installed product
17.5 mm
- Power
 - Total power loss under IN
5.8 W
- Endurance
 - Electric endurance in number of cycles
1000
 - Number of mechanical operations
20000
- Capacity
 - Number of modules
1
- Installation, mounting
 - Tightening torque
1,9Nm
- Connection
 - Type of connection
with screw
- Standards
 - Standard text
EN 60898-1
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-25/80 °C
- Temperature
 - Operating temperature
-25/70 °C