

JK118BG

125A 18 Way TPN Board Glazed Door

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Main electrical features

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Dimensions

| | |
|----------------------------|----------|
| Depth of installed product | 132.5 mm |
|----------------------------|----------|

| | |
|-----------------------------|---------|
| Height of installed product | 1100 mm |
|-----------------------------|---------|

| | |
|----------------------------|--------|
| Width of installed product | 465 mm |
|----------------------------|--------|

Cover, door

| | |
|----------------------|-------------------|
| Type of door closing | Quarter turn lock |
|----------------------|-------------------|

| | |
|--------------|----------|
| Door locking | with key |
|--------------|----------|

| | |
|---------------|----|
| Interlockable | No |
|---------------|----|

Materials

| | |
|--------|----------|
| Colour | RAL 7035 |
|--------|----------|

| | |
|--------|-------|
| Colour | beige |
|--------|-------|

Technical characteristics JK118BG2

| | |
|-------------------|------------------|
| RAL colour | RAL 1001 - Beige |
| RAL colour number | 7035 |
| Material | Steel |

Equipment

| | |
|---------------------|----|
| Can be accessorized | No |
|---------------------|----|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|----------------------|
| Protection index IP | IP30 |
| Protection class | Protection class III |
