



Time switch daily cycle with reserve 3 modules

Technical Characteristics

Fixing mode	Din-Rail
Power reserve	≈ 200 h
Switch mode	change-over contact, usable as NC or NO
Rated operational voltage U _e	230 V
Frequency	50 Hz
Supply voltage	230V AC
Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	54 mm
Dimensions (W x H x D)	90 mm 54 mm 60 mm
Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under I _N	1 W
Power dissipation per coil	0.5 W
Breaking capacity	16A 250V AC1
Number of modules	3
Charging time of the power reserve in hours	120
Max. power with incandescent lamps	900 W
Mounting type	surface-mounted
Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Programming cycle	24H
Setting	Setting via day dial
Number of channels	1
Supply failure reserve	200 h
Cycle	daily
Protection index IP	IP20

Operating temperature

-10 °C
45 °C

Working accuracy

1