



IP55 Motion Detector Comfort 220° Anthracite

Technical Characteristics

| | |
|---------------------------------------|--|
| Fixing mode | surface-mounting |
| Function | can be used as a single unit, main device or extension unit Presence simulation |
| Frequency | 50/60 Hz |
| Height of installed product | 2.5 m |
| Dimensions (W x H x D) | 153 mm 139 mm 91 mm |
| Incandescent bulb power | 2300 W |
| Breaking capacity | 16A 250V AC1 |
| Cover | with cover elements to limit the detection field |
| Supply voltage | 230 V +10% / -15% |
| Detection angle | 220 ° |
| Colour | charcoal |
| Brightness measurement range | 5 Lux 1000 Lux |
| Maximum Mounting Height | 4 m |
| Connection type | quick connect |
| Type of contacts | contact floating |
| Type of connection | with screw terminals |
| Time delayed range | 5s to 30 min |
| Setting | with potentiometers for setting the response brightness and delay time without dismantling |
| Response value sensitivity adjustable | Yes |
| Component | with fitting material |
| Remote controllable | EE806 |
| Protection index IP | IP55 |
| Operating temperature | -20 °C 55 °C |
| Application, usage | Motion detector |