

HEC251H

Moulded Case Circuit Breaker h250 4P 70kA 250A LSI



- Architecture
 - Number of poles
4 P
 - Type of pole
4P4D N:0;50;100%
- Main electrical features
 - Rated operational voltage U_e
220 / 690 V
 - Frequency
50;60 Hz
 - Rated current
250 A
- Voltage
 - Rated insulation voltage
800 V
 - Rated impulse withstand voltage
8000 V
- Power
 - Total power loss under I_N
73.2 W
- Endurance
 - Electric endurance in number of cycles
1000
 - Number of mechanical operations
4000
- Capacity
 - Number of modules

8

- Cover, door
 - Interlockable
No
- Installation, mounting
 - Tightening torque
12Nm
- Connection
 - Connection cross-sect. flexible conductor
35 ; 150mm²
 - Connection cross-sect. rigid cable
35 ; 185mm²
 - Type of connection
Terminal
- Equipment
 - Number of auxiliary contacts as normally closed contact
0
 - Number of auxiliary contacts as normally open contact
0
 - Number of auxiliary contacts as change-over contact
0
 - Can be accessorized
No
- Standards
 - Standard text
IEC 60947-2
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP4X
- Use conditions
 - Storage temperature
-35/70 °C
- Temperature
 - Operating temperature
-25/70 °C