

# ADC116

RCBO Electronic 1M 1P 10kA C-16A 30mA AC Class



- Architecture
  - Neutral position right
  - Number of poles 1 P
  - Type of pole 1 P
  - Curve C
- Main electrical features
  - Frequency 50 Hz
  - Rated current 16 A
- Voltage
  - Rated insulation voltage 250 V
  - Max operating voltage 253 V
  - Rated impulse withstand voltage 4000 V
- Electric current
  - Breaking and opening capacity 6 kA
- Electric current / temperature
  - Rating current 30°C 16 A

- Dimensions
  - Depth of installed product  
73 mm
  - Height of installed product  
115 mm
  - Width of installed product  
17.8 mm
- Power
  - Total power loss under IN  
4.74 W
- Endurance
  - Electric endurance in number of cycles  
2000
  - Number of mechanical operations  
1000
- Capacity
  - Number of modules  
1
- Installation, mounting
  - Tightening torque  
2,1Nm
- Standards
  - Standard text  
EN 61009-1  
IEC 61009-1
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP20
  - Residual current type  
AC
- Temperature
  - Operating temperature  
-5/60 °C