

MTN110

MCB 1P 6kA B-10A 1M

Architecture

Neutral position	not applicable
Number of poles	1 P
Type of pole	1 P
Fixing mode	DIN rail type O (symmetrical)
Curve	B

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50;60 Hz
Rated current	10 A
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated service breaking capacity Ics AC according IEC 60898-1 6 kA

Electric current / temperature

Rating current 30°C	10 A
---------------------	------

Dimensions

Depth of installed product	70 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.5 mm
----------------------------	---------

Power

Total power loss under IN	2.75 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	4000
--	------

Number of mechanical operations	20000
---------------------------------	-------

Capacity

Number of modules	1
-------------------	---

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 ; 25mm ²
---	-----------------------

Connection cross-sect. rigid cable	1 ; 35mm ²
------------------------------------	-----------------------

Type of connection	with screw
--------------------	------------

Equipment

Quick connect	no
---------------	----

Standards

Standard text	EN 60898-1
---------------	------------

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25/70 °C
-----------------------	-----------

Storage temperature	-25/80 °C
---------------------	-----------

Temperature

Operating temperature	-25/70 °C
-----------------------	-----------
