



Timer

Technical Characteristics

Fixing mode	DIN rail type O (symmetrical)
Function	Functions: On delay, Off delay, single shot leading edge; single shot trailing edge, pulse shaping, flashing symmetrically, contact open; closed
Switch mode	change-over contact, usable as NC or NO
Frequency	50/60 Hz
Supply voltage	12, 24, 48 or 230V
Depth of installed product	58 mm
Height of installed product	85 mm
Length	64 mm
Width of installed product	17.5 mm
Dimensions (W x H x D)	85 mm 17.5 mm 58 mm
Power consumed	15 VA
Power consumption (operation)	15 VA
Total power loss under IN	2 W
Power dissipation per coil	0.5 W
Breaking capacity	8A 230V AC1
Number of modules	1
Max. power with incandescent lamps	450 W
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Time delayed range	0.1 s... 10 h
Setting	with 2 potentiometers for setting of delay time
Protection index IP	IP40

Operating temperature

-20 °C
50 °C