



ADA320G

**RCBO Electronic 1P 6kA B Curve -20A, 30mA Type A(AC & Pulsating DC Sensitive)1M**

**Technical characteristics**

**Architecture**

Type of pole	1P
Curve	B

**Electric current**

Rated current	20 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	26.63 A
Rated current at -20°C	26.13 A
Rated current -15°C	25.64 A
Rated current -10°C	25.54 A
Rated current -5°C	24.65 A
Rated current at 0°C	24.16 A
Rated current 5°C	23.66 A
Rated current 10°C	23.17 A
Rated current 15°C	22.67 A
Rated current at 20°C	22.18 A
Rated current 25°C	21.68 A
Rated current 30°C	20 A
Rated current 35°C	20.69 A
Rated current at 40°C	20.20 A
Rated current at 50°C	20 A
Rated current 55°C	18.72 A
Rated current 60°C	18.22 A
Correction factor of rating current for 2 devices placed side by side	0.95
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Main electrical attributes**

### Voltage

Rated insulation voltage Ui	250 V
Rated impulse withstand voltage Uimp	4,000 V
Max. operating voltage	253 V
Rated operational voltage Ue	230 - 230 V
Overtoltage category according to IEC 60947-1	3

### Power

Total power loss under IN	5.19 W
---------------------------	--------

### Frequency

Frequency	50 - 50 Hz
-----------	------------

### Use conditions

Max. Altitude	2,000 m
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-20 - 70 °C
Storage/transport temperature	-25 - 80 °C

### Endurance

Electric endurance in number of cycles	16,000
Number of mechanical operations	20,000

### Connection

Cross-section of input with screws, for flexible conductors	1 - 10 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 16 mm <sup>2</sup>

### Installation, mounting

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	Screw terminal

### Capacity

Number of modules	1
-------------------	---

### Dimensions

Height	92 mm
Width	17.70 mm
Depth	70 mm

### Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----