

MCN316A

MCB 3P 6kA C-16A 3M



- Architecture
 - Number of poles
3 P
 - Type of pole
3 P
 - Curve
C
- Main electrical features
 - Frequency
50/60 Hz
 - Rated current
16 A
 - Type of supply voltage
AC
- Voltage
 - Rated insulation voltage
500 V
 - Rated impulse withstand voltage
4000 V
- Electric current
 - Rated service breaking capacity Ics AC according IEC 60898-1
6 kA
- Electric current / temperature
 - Rating current 30°C
16 A
- Dimensions
 - Depth of installed product

- 70 mm
- Height of installed product
83 mm
- Width of installed product
52.5 mm
- Power
 - Total power loss under IN
6.99 W
- Endurance
 - Electric endurance in number of cycles
4000
 - Number of mechanical operations
20000
- Capacity
 - Number of modules
3
- Installation, mounting
 - Tightening torque
2,8Nm
- Connection
 - Connection cross-sect. flexible conductor
1 / 25mm²
 - Connection cross-sect. rigid cable
1 / 35mm²
 - Type of connection
with screw
- Standards
 - Standard text
EN 60898-1
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-25/80 °C
- Temperature
 - Operating temperature
-25/70 °C