

ARC513U

MCB with dangerous arc detection 1P+N 10kA B-13A 2M



- Architecture
 - Neutral position right
 - Number of poles 2 P
 - Type of pole 1P+N
 - Curve B
- Main electrical features
 - Rated operational voltage U_e 230 V
 - Rated current 13 A
 - Type of supply voltage AC
- Voltage
 - Rated insulation voltage 500 V
 - Max operating voltage 253 V
 - Rated impulse withstand voltage 4 kV
- Electric current
 - Rated service breaking capacity I_{cs} AC according IEC 60898-1 7.5 kA
- Electric current / temperature

- Rating current 30°C
13 A
- Dimensions
 - Depth of installed product
70 mm
 - Height of installed product
85 mm
 - Width of installed product
35.5 mm
- Power
 - Total power loss under IN
4.24 W
- Endurance
 - Electric endurance in number of cycles
2000
 - Number of mechanical operations
4000
- Capacity
 - Number of modules
2
- Installation, mounting
 - Tightening torque
2Nm
- Accessories included
 - Type of accessory
AFDD
- Equipment
 - Quick connect
no
 - Can be accessorized
Yes
- Standards
 - Standard text
EN 62606 ; IEC 60898-1
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-40/70 °C
- Temperature
 - Operating temperature
-25/60 °C