



### Fuse carrier 2P 1000V DC L38 2M

#### Technical Characteristics

Number of poles	2 P
Type of pole	2 P
Indicator lamp	no
Rated operational voltage Ue	1000 V 690 V
Frequency	50/60 Hz
Rated current	32 A
Type of supply voltage	DC
Rated insulation voltage	690 V
Depth of installed product	75 mm
Height of installed product	77 mm
Width of installed product	35 mm
Total power loss under IN	2.2 W
Electric endurance in number of cycles	2000
Number of mechanical operations	4000
Number of modules	2
Interlockable	No
Tightening torque	2Nm
Connection cross-sect. flexible conductor	0,75 / 10mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 16mm <sup>2</sup>
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	50 °C -25 °C