

EG203E

Digital time switch weekly cycle 2 channels Evolution



Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Switch mode	2 x change-over contact
-------------	-------------------------

Main electrical features

Rated operational voltage Ue	195 / 230 / 265 V
------------------------------	-------------------

Frequency	50 Hz
-----------	-------

Voltage

Supply voltage	230V AC
----------------	---------

Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	35 mm
----------------------------	-------

Dimensions (W x H x D)	35/85/64 mm
------------------------	-------------

Power	
Power consumed	6 VA
Total power loss under IN	4 W
Power dissipation per coil	0.5 W

Capacity	
Breaking capacity	16A 250V AC1

Capacity	
Number of modules	2

Battery	
Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

Incandescent bulbs control	
Max. power with incandescent lamps	2300 W

Connection	
Connection cross-sect. flexible conductor	1 ; 16mm ²
Connection cross-sect. rigid cable	1,5 ; 10mm ²
Type of connection	with screw
Number of contacts	2
Type of contacts	2 changeovers
Type of connection	with screw terminals

Settings	
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	2X7D.

Equipment	
Number of program steps	56
Number of channels	2
Supply failure reserve	5 years
With holidays program	Yes
DCF	No

Use	
Cycle	weekly

Safety	
Protection index IP	IP20

Use conditions	
Operating temperature	-5/45 °C
Working accuracy	1,5

Storage temperature	-20/70 °C
---------------------	-----------

Temperature

Operating temperature	-5/45 °C
-----------------------	----------
