

# EG203

Weekly digital time switch 2 channels, digital, 2 modules



## Architecture

Fixing mode Din-Rail

## Configuration

Switch mode 2 x change-over contact

## Main electrical features

Rated operational voltage Ue 195 / 230 / 265 V

Frequency 50 Hz

## Voltage

Supply voltage 230V AC

## Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Width of installed product 35 mm

Dimensions (W x H x D) 35/85/64 mm

Power	
Power consumed	6 VA
Total power loss under IN	4 W
Power dissipation per coil	0.5 W

Capacity	
Breaking capacity	16A 250V AC1

Capacity	
Number of modules	2

Battery	
Power reserve [years]	≈ 5 a
Charging time of the power reserve in hours	0

Incandescent bulbs control	
Max. power with incandescent lamps	2300 W

Connection	
Connection cross-sect. flexible conductor	1 ; 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 ; 10mm <sup>2</sup>
Type of connection	with screw
Number of contacts	2
Type of contacts	2 changeovers
Type of connection	with screw terminals

Settings	
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital
Programming cycle	2X7D.

Equipment	
Number of program steps	56
Number of channels	2
Supply failure reserve	5 years
With holidays program	No
DCF	No

Use	
Cycle	weekly

Safety	
Protection index IP	IP20

Use conditions	
Operating temperature	-5/45 °C
Working accuracy	1,5

---

Storage temperature	-20/70 °C
---------------------	-----------

---

Temperature

Operating temperature	-5/45 °C
-----------------------	----------

---