



ADA916U

**RCBO 1P+N 6kA B-16A 30mA A Class**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Curve	B

**Main electrical features**

Rated operational voltage Ue	240 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	30 mA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

**Electric current / temperature**

Rating current 30°C	16 A
---------------------	------

**Dimensions**

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under IN	5.2 W
---------------------------	-------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Installation, mounting**

Tightening torque	2,1Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 25mm <sup>2</sup>
Type of connection	with screw

---

**Standards**

Standard text	IEC 61009-1
---------------	-------------

---

**Safety**

Residual current type	A
-----------------------	---

---

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------