

EPN525

Latching relay 2NC+2NO 230V



Main electrical features

Rated operational voltage Ue	250 V
Frequency	50;60 Hz
Rated current	16 A

Voltage

Rated insulation voltage	400 V
--------------------------	-------

Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power

Total power loss under IN	2.4 W
---------------------------	-------

Endurance

Number of mechanical operations	500000
---------------------------------	--------

Capacity

Number of modules 2

Installation, mounting

Tightening torque 1,6Nm

Connection

Connection cross-sect. flexible conductor 1 ; 6mm²

Connection cross-sect. rigid cable 1,5 ; 10mm²

Type of connection with screw

Number of contacts 4

Type of contacts 2NC+2NO

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Storage temperature -40/80 °C

Temperature

Operating temperature -5/40 °C
