



Yearly time switch 4 channels, digital, 4 modules

Technical Characteristics

Fixing mode	Din-Rail
Function	Keylock via PIN code Presence simulation with pulse function with operating hours meter
Switch mode	2 x change-over contact and 2 x NO contact
Rated operational voltage Ue	230 V 195 V 253 V
Frequency	50/60 Hz
Supply voltage	230V +10% / -15%
Depth of installed product	65 mm
Height of installed product	90 mm
Width of installed product	70 mm
Dimensions (W x H x D)	90 mm 65 mm 70 mm
Power consumed	2 VA
Total power loss under IN	2 W
Breaking capacity	10A 250V AC1
Number of modules	4
Power reserve [years]	≈ 5 a
Max. power with incandescent lamps	1500 W
Mounting type	din-Rail
Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of connection	quick connect
Number of contacts	4
Type of contacts	2 changeover + 2NO
Type of connection	with QuickConnect plug-in terminals
Summer / Winter time change	automatic
Shortest switching time	1 mn
Type of programming	digital, with programming key
Programming cycle	yearly
Number of channels	4

Supply failure reserve	5 years
With holidays program	Yes
DCF	Yes
Cycle	yearly
Protection index IP	IP20
Operating temperature	-10 °C 50 °C
Working accuracy	+ 0,2 s / 24h