



ADA932U

RCBO 1P+N 6kA B-32A 30mA A Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Curve	B

Main electrical features

Rated operational voltage U_e	240 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
Rated short circuit breaking capacity I_{cn} under 230V AC according IEC60898-1	6 kA

Electric current / temperature

Rating current 30°C	32 A
---------------------	------

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power

Total power loss under I_N	8.3 W
------------------------------	-------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	2,1Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 16mm ²
Connection cross-sect. rigid cable	1 / 25mm ²

Type of connection with screw

Standards

Standard text IEC 61009-1

European directive WEEE concerned

Safety

Protection index IP IP20

Residual current type A

Use conditions

Operating temperature -25...40 °C