

HEC041G

h3 MCCB h250 4x40A Plug In 50kA



- Architecture
 - Number of poles
4 P
 - Type of pole
4P4D N:0;50;100%
- Main electrical features
 - Frequency
50/60 Hz
 - Rated current
40 A
- Voltage
 - Rated insulation voltage
800 V
 - Rated impulse withstand voltage
8000 V
- Endurance
 - Electric endurance in number of cycles
1000
 - Number of mechanical operations
4000
- Capacity
 - Number of modules
8
- Cover, door
 - Interlockable
No
- Installation, mounting

- Tightening torque
12Nm
- Connection
 - Connection cross-sect. flexible conductor
35 / 150mm²
 - Connection cross-sect. rigid cable
35 / 185mm²
 - Type of connection
Terminal
- Equipment
 - Can be accessorized
No
- Standards
 - Standard text
IEC 60947-2
 - European directive WEEE
not concerned
- Safety
 - Protection index IP
IP4X
- Use conditions
 - Storage temperature
-35/70 °C
- Temperature
 - Operating temperature
-25/70 °C