



Moulded Case Circuit Breaker h250 3P 50kA 250A LSI

Technical Characteristics

Number of poles	3 P
Type of pole	3P3D
Rated operational voltage Ue	220 V 690 V
Frequency	50/60 Hz
Rated current	250 A
Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V
Total power loss under I _N	73.2 W
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Number of modules	6
Interlockable	No
Tightening torque	12Nm
Connection cross-sect. flexible conductor	35 / 150mm ²
Connection cross-sect. rigid cable	35 / 185mm ²
Type of connection	Terminal
Can be accessorized	No
Standard text	IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP4X
Operating temperature	-25 °C 70 °C