



ADA956U

**RCBO 1P+N 6kA C-6A 30mA A Class**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Curve	C

**Main electrical features**

Rated operational voltage Ue	240 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	30 mA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

**Electric current / temperature**

Rating current 30°C	6 A
---------------------	-----

**Dimensions**

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under IN	1.9 W
---------------------------	-------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Connection**

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
---	-----------------------

**Standards**

Standard text	IEC 61009-1
---------------	-------------

**Safety**

---

Protection index IP	IP20
Residual current type	A

---

**Use conditions**

---

Operating temperature	-25...40 °C
-----------------------	-------------

---