

HEJ401DR

Moulded Case Circuit Breaker h3 x630 TM ADJ 4P4D N0-100% 400A 70kA FTC

:hager

- Architecture
 - Neutral position
left
 - Number of poles
4 P
 - Type of pole
4P4D N:0;100%
 - Fixing mode
fixing plate
- Main electrical features
 - Frequency
50/60 Hz
 - Rated current
400 A
 - Type of supply voltage
AC
- Voltage
 - Rated insulation voltage
690 V
 - Rated impulse withstand voltage
8 kV
- Electric current
 - Rated service breaking capacity Ics under 400V AC according IEC 60947-2
70 kA
- Dimensions
 - Depth of installed product
150 mm

- Height of installed product
260 mm
- Width of installed product
185 mm
- Power
 - Total power loss under IN
116 W
- Tripping
 - Short-time delayed tripping
No
- Cover, door
 - Interlockable
No
- Installation, mounting
 - Tightening torque
18Nm
- Connection
 - Type of connection
Terminal
- Cable
 - Cable Material
Cu
- Equipment
 - Can be accessorized
Yes
- Standards
 - Standard text
IEC 60947-2
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP4X