

HDA098Z

Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 100A 18kA CTC



- Architecture
 - Neutral position without neutral
 - Number of poles 1 P
 - Type of pole 1P1D
 - Fixing mode DIN rail type O or type J
- Main electrical features
 - Frequency 50/60 Hz
 - Rated current 100 A
- Voltage
 - Rated insulation voltage 690 V
 - Rated impulse withstand voltage 8000 V
- Electric current
 - Rated service breaking capacity I_{cs} under 400V AC according IEC 60947-2 18 kA
- Dimensions
 - Depth of installed product 68 mm
 - Height of installed product 130 mm

- Width of installed product
25 mm
- Power
 - Total power loss under IN
8.4 W
- Tripping
 - Short-time delayed tripping
No
- Endurance
 - Electric endurance in number of cycles
1000
 - Number of mechanical operations
4000
- Cover, door
 - Interlockable
No
- Connection
 - Type of connection
with screw
- Equipment
 - Can be accessorized
Yes
- Standards
 - Standard text
IEC 60947-2
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP4X