



### Multifunction stair case time lag switch

#### Technical Characteristics

Fixing mode	Din-Rail
	195 V
	230 V
	253 V
Rated operational voltage Ue	
Frequency	50/60 Hz
Rated current	16 A
Supply voltage	230V AC
Acceptable current rating with AC1	16 A
Depth of installed product	64 mm
Length	64 mm
Width of installed product	17.5 mm
Max. power with fluo uncompensated lamps	3600 VA
Power consumed	1 VA
Total power loss under IN	2 W
Power dissipation per coil	0.25 W
Number of modules	1
Supply voltage	230 V
Max. power with fluorescent parallel lamps	1000 VA
Max. power with incandescent lamps	2300 W
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of connection	with screw
Connection type	3 and 4 wires
Number of contacts	1
Type of contacts	1NO
Time delayed range	30s ; 10min
Protection index IP	IP20