

ERC218

Relay 16A, 1NO+1NC, 230V~50Hz

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz
Rated current	16 A

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4 kV

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

Power

Total power loss under IN	3.9 W
Power dissipation per coil	2.9 W

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	100000
Capacity	
Number of modules	1
Fluorescent bulbs control	
Max. power with fluorescent parallel lamps	490 VA
Incandescent bulbs control	
Max. power with incandescent lamps	1100 W
Installation, mounting	
Tightening torque	1,2Nm
Connection	
Connection cross-sect. flexible conductor	1 ; 6mm ²
Connection cross-sect. rigid cable	1 ; 10mm ²
Type of contacts	1NC+1NO
Equipment	
Can be accessorized	Yes
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	2
Use conditions	
Storage temperature	-40/80 °C
Temperature	
Operating temperature	-10/50 °C