

L502PV

Fuse carrier 2P 1000V DC L38 2M



- Architecture
 - Number of poles
2 P
 - Type of pole
2 P
- Controls and indicators
 - Indicator lamp
no
- Main electrical features
 - Rated operational voltage Ue
690 / 1000 V
 - Frequency
50;60 Hz
 - Rated current
32 A
 - Type of supply voltage
DC
- Voltage
 - Rated insulation voltage
690 V
- Dimensions
 - Depth of installed product
75 mm
 - Height of installed product
77 mm
 - Width of installed product
35 mm

- Power
 - Total power loss under IN
2.2 W
- Endurance
 - Electric endurance in number of cycles
2000
 - Number of mechanical operations
4000
- Capacity
 - Number of modules
2
- Cover, door
 - Interlockable
No
- Installation, mounting
 - Tightening torque
2Nm
- Connection
 - Connection cross-sect. flexible conductor
0,75 ; 10mm²
 - Connection cross-sect. rigid cable
1 ; 16mm²
- Equipment
 - Can be accessorized
No
- Standards
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-25/80 °C
- Temperature
 - Operating temperature
-25/50 °C