



Contactor 63A 2NO 230V

Technical Characteristics

Rated operational voltage Ue	400 V
Frequency	50/60 Hz
Rated insulation voltage	400 V
Rated impulse withstand voltage	4 kV
Acceptable current rating with AC1	63 A
Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	52.5 mm
Contact rating with 230 V in AC1	13500 W
Total power loss under IN	10.7 W
Power dissipation per coil	0.67 W
Electric endurance in number of cycles	30000
Number of mechanical operations	1000000
Number of modules	3
Max. power with fluorescent parallel lamps	1800 VA
Max. power fluo. duo lamp comp. series	3500VA
Max. power with incandescent lamps	6500 W
Connection cross-sect. flexible conductor	4 / 16mm ²
Connection cross-sect. rigid cable	4 /25mm ²
Type of connection	with screw
Number of contacts	2
Type of contacts	2NO
Can be accessorized	No
European directive WEEE	not concerned
Protection index IP	IP20